




# **VIAVI**

# **CleanBlast™ System Portable**

Advanced fiber optic connector end-face cleaning system

The patented VIAVI Solutions® CleanBlast fiber end-face cleaning system provides a fast, effective, and cost-efficient solution for removing dirt and debris from connectors in most common applications. CleanBlast is a non-contact system that uses a highly filtered stream of pressurized gas with a vacuum circuit to create a high-flow-rate jet across the fiber's surface. A 30 µl cleaning solvent is injected into the airflow, and the contamination from the end face along with the solvent are then removed through the retrieval circuit. The precise, highly efficient non-contact air-solvent-air stream blasts and removes contamination with nearly 100% effectiveness.



### **Key Benefits**

- Provides rapid, controlled, and repeatable cleaning and removal of contamination from fiber end faces
- Eliminates user sensitivity and error
- Removes, rather than spreads or smears, loose debris from fiber end faces at the push of a button

#### **Key Features**

- Uses a precise non-contact air-solvent-air mixture/sequence to blast and remove contamination particles
- Offers a comprehensive selection of precision cleaning tips and adapters
- Input for optional FBP probe microscope and LCD display for fiber inspection capability

### **Applications**

- Clean various types of both male (patch cord) and female (bulkhead) connector ends including SC, FC, LC, ST, E2000, MPO, MTP®, MPX, MT, and SMA
- Quickly and easily remove contamination, dust, lint, oil, and other forms of debris from fiber optic end faces
- Clean multiple configurations and connector types with interchangeable, precision cleaning tips and adapters

#### **Overview**

VIAVI portable CleanBlast systems include a mobile base unit (built-in compressor) housed in a durable, rugged Pelican<sup>™</sup> transport case with a handset connected to a 5 ft umbilical for optimal reach. Precision cleaning tips are available for both male (patch cord) and female (bulkhead) connectors for various connector types including SC, LC, FC, ST, E2000, MPO, MPX, MT, and SMA. All models include an input port for a separate probe microscope for fiber inspection capabilities and a video output for connecting to an external monitor or to a mounted LCD.


The system's cleaning solvent reservoir holds enough solution for at least 8,000 cleaning cycles. The solvent refill process is simple and spill-resistant. A built-in safety feature prevents the handset from accidentally triggering the system. It also monitors solvent levels and the safety switch, and features a series of LEDs to indicate system status.

## **FCLT Cleaning Tips**


VIAVI offers a complete selection of precision cleaning tips and adapters for every connector and application including SC, FC, ST, LC, MU, E2000, and MPO/MTP connectors.



CleanBlast vs. Traditional Swab/Stick




#### **Components and Functions**





Portable CleanBlast system with FBP probe and LCD



# **Specifications**

| Parameter           | Description  |  |
|---------------------|--|--|
| CleanBlast—Portable |  |  |
| Dimensions          | 40 x 33 x 18 cm (16 x 13 x 7 in)   |  |
| Weight              | 9.5 kg (21 lb)   |  |
| Power requirements  | 100-240 V AC, 2 A  |  |
| Air source          | Internal compressor, regulated output 40 psi.                                  |  |
| Solvent consumption | At least 8,000 cleaning cycles per refill                                      |  |
| Maintenance         | 50,000 cycles per air filter change, requires 2 x 0.01 μ air filters (included |  |
|                     | and installed)   |  |
| Video output        | BNC or DIN connector to optional LCD   |  |
| Cleaning cycle time | 5 s  |  |

## **Ordering Information**

| Description   |   | Part Number   |
|---|---|---------------|
| CleanBlast Syst   | tems  |               |
| CleanBlast portable kit with dual-magnification (200/400X) FBP probe microscope, TFT LCD, 8 FBPT inspection tips (SC, SC-APC, FC, ST, LC bulkhead tips, and universal 2.5 mm UPC, 2.5 mm APC, 1.25 mm UPC patch cord tips), and 4 cleaning tips and adapters (universal 2.5 mm, 1.25 mm and 2.5 mm bulkhead tips, and 1.25 mm patch cord mating adapters) |   | FCL-P1005     |
| CleanBlast port   | FCL-P1005-EU  |               |
| probe microsco  |   |               |
| bulkhead tips a   |   |               |
| tips), 4 cleaning   |   |               |
|   | nm patch cord mating adapters) table with 5 ft umbilical bulkhead handset with universal 2.5 mm | 501 8444      |
|   | FCL-P1000   |               |
| cleaning tip  |   | FCI D1000 FII |
| CleanBlast–portable with 5 ft umbilical bulkhead handset with universal 2.5 mm cleaning tip and EU power supply   |   | FCL-P1000-EU  |
| CleanBlast—portable with 5 ft umbilical and 90 degree bulkhead handset with   |   | FCL-P2000     |
| universal 2.5 mr  | 3   | TCL 1 2000    |
| Cleaning tips*  | Universal 2.5 mm bulkhead (for CleanBlast)  | FCLT-U25      |
|   | Universal 2.5 mm patch cord mating adapter  | FCLT-U25MA    |
|   | Universal 1.25 mm bulkhead (for CleanBlast)   | FCLT-U12      |
|   | Universal 1.25 mm patch cord mating adapter   | FCLT-U12MA    |
|   | MTP/MPO bulkhead (for CleanBlast)   | FCLT-MTP      |
|   | MTP patch cord mating adapter   | FCLT-MTP-MA   |
| Replacement   | Internal air filter; 0.01U 0.125 inch NPTF  | FCLP-FA-F1    |
| parts   | Bottle cap refill assembly  | FCLP-RCA-1    |
|   | CleanBlast solvent refill, single bottle, 225 ml  | FCLP-SOL1     |
|   | CleanBlast solvent refill, 6-pack, 225 ml   | FCLP-SOL1-6   |
|   | LCD video display with mounting bracket and base  | VM-LCD-6      |

<sup>\*</sup> VIAVI has over 300 tips, patch cords, and adapters available for inspecting and cleaning different fiber optic connectors for a variety of different applications. This is not an all-inclusive list, but solutions for the most common connectors and applications. Please contact VIAVI for more information.





Contact Us

**+1 844 GO VIAVI** (+1 844 468 4284)

To reach the VIAVI office nearest you, visit viavisolutions.com/contacts.

VIAVI Vertriebspartner: tso GmbH Hermann-Köhler-Str.13 • 58553 Halver Büro Frechen Augustinusstraße 9d • 50226 Frechen © 2018 VIAVI Solutions Inc. Product specifications and descriptions in this document are subject to change without notice. fclp-ds-fit-tm-ae 30162631 903 0318

T +49 (0) 23 53 / 66987 - 0 F +49 (0) 23 53 / 66987 - 29 info@tso-gmbh.de

www.tso-gmbh.de